

# DS2


## SOLENOID OPERATED DIRECTIONAL CONTROL VALVE

**SERIES 10** 

## SUBPLATE MOUNTING ISO 4401-02

p max 350 barQ max 25 l/min

#### **MOUNTING INTERFACE**




#### **PERFORMANCES**

(obtained with mineral oil with viscosity of 36 cSt at 50°C)

Maximum operating pressure: - ports P - A - B - port T	bar	350 250		
Maximum flow rate	l/min	25		
Pressure drop ∆p-Q	see p	aragraph 4		
Operating limits	see paragraph 5			
Electrical features	see paragraph 7			
Electrical connections	EN 175301-803 (ex DIN 43650)			
Ambient temperature range	°C -20 / +50			
Fluid temperature range	°C -20 / +80			
Fluid viscosity range	cSt 10 ÷ 400			
Fluid contamination degree	According to ISO 4406:1999 class 20/18/15			
Recommended viscosity	cSt 25			
Mass: single solenoid valve double solenoid valve	kg	0.9 1.3		


#### **OPERATING PRINCIPLE**




- Direct acting, subplate mounting directional control valve, with mounting surface according to ISO 4401 standards.
- Compact design with reduced solenoid dimensions, suitable for mini-power packs and mobile and agricultural applications.
- The valve body is made with high strenght viton castings provided with wide internal passages in order to minimize the flow pressure drop. Wet armature solenoids with interchangeable coils are used (for further information on solenoids see paragraph 7).
  - The valve is supplied with 4 way designs, with 2 or 3 positions and with several interchangeable spools with different porting arrangements.
  - The valve is available with direct current solenoids.
  - The valve is also available with zinc-nickel coating that ensures a salt spray resistance up to 240 hours.

41 110/118 ED 1/6

#### 1 - IDENTIFICATION CODE



### 2 - SPOOL TYPE



41 110/118 ED 2/6




#### 3 - HYDRAULIC FLUIDS

Use mineral oil-based hydraulic fluids HL or HM type, according to ISO 6743-4. For these fluids, use NBR seals (code N). For fluids HFDR type (phosphate esters) use FPM seals (code V). For the use of other fluid types such as HFA, HFB, HFC, please consult our technical department.

Using fluids at temperatures higher than 80 °C causes a faster degradation of the fluid and of the seals characteristics. The fluid must be preserved in its physical and chemical characteristics.


#### 4 - PRESSURE DROPS △P-Q

(obtained with viscosity 36 cSt at 50 °C)



## **ENERGIZED VALVE**

	FLOW DIRECTIONS				
SPOOL	P→A	Р→В	А→Т	В→Т	
	CURVES ON GRAPHS				
S1, SA1, SB1	1	1	2	2	
S2, SA2, SB2	1	1	2	2	
S3, SA3, SB3	1	1	1	1	
S4, SA4, SB4	4	4	5	5	
TA	2	1	2	3	




#### SOLENOID VALVE CENTRAL POSITION

	FLOW DIRECTIONS				
SPOOL	P→A	Р→В	А→Т	В→Т	P→T
	CURVES ON GRAPHS				
S2	-	-	-	-	1
S3,	-	-	2	2	-
S4	-	-	-	-	2

#### **5 - OPERATING LIMITS**

The curves define the flow rate operating fields according to the valve pressure of the different versions. The operating limits can be considerably reduced if a 4-way valve is used as 3-way valve with port A or B plugged or without flow.

The values have been obtained according to ISO 6403 norm with solenoids at rated temperature and supplied with voltage equal to 90% of the nominal voltage. The value have been obtained with mineral oil, viscosity 36 cSt, temperature 50 °C and filtration according to ISO 4406:1999 class 18/16/13.



SPOOL	CURVE
S1, S2, S3, TA, TB	1
S4	2

41 110/118 ED 3/6



## DS2 SERIES 10

#### 6 - SWITCHING TIMES

The values indicated are obtained according to ISO 6403 standard, with mineral oil viscosity 36 cSt at 50°C.

TIMES (±10%) [ms]				
ENERGIZING DE-ENERGIZING				
25 ÷ 75	15 ÷ 25			

#### 7 - ELECTRICAL FEATURES

#### 7.1 - Solenoids

These are essentially made up of two parts: tube and coil. The tube is threaded into the valve body and includes the armature that moves immersed in oil, without wear. The inner part, in contact with the oil in the return line, ensures heat dissipation. The interchangeability of coils of different voltages is allowed within the same type of supply current, alternating or direct.

The coil is fastened to the tube by a threaded ring, and can be rotated 360°, to suit the available space.

#### Protection from atmospheric agents IEC 60529

The IP protection degree is guaranteed only with both valve and connectors of an equivalent IP degree, correctly connected and installed.

electric connection	electric connection protection	whole valve protection
K1 EN 175301-803 (ex DIN 43650)	IP65	
K2 AMP JUNIOR	IP65/IP67	IP65
K7 DEUTSCH DT04 male	IP65/IP67	

#### 7.2 - Current and power consumption

In direct current energizing, current consumption stays at fairly constant values, essentially determined by Ohm's law:  $V = R \times I$ 

The table shows current and power consumption values related to coil types.

(values +10 %)

(values ±10 70)						
	Resistance at 20°C	Current consumption	Power consuption	Coil code		
	[Ω]	[A]	[W]	K1	K2	<b>K</b> 7
D12	4.98	2.41	28.9	1903560	1903640	1903650
D24	21	1.15	28	1903561	1903641	1903651

#### 8 - ELECTRIC CONNECTORS


The solenoid valves are not supplied with connector. Connectors type EN 175301-803 (ex DIN 43650) for K1 connections can be ordered separately. For the identification of the connector type to be ordered, please see catalogue 49 000.

#### 9 - INSTALLATION

The valves can be mounted in any position.

Valve fitting takes place by means of screws or tie rods, fixing the valve on a lapped surface, with values of planarity and smoothness that are equal to or better than those indicated in the drawing.

If the minimum values of planarity or smoothness are not met, fluid leakages between valve and mounting surface can easily occur.




SUPPLY VOLTAGE FLUCTUATION ±10% Vnom MAX SWITCH ON FREQUENCY 10.000 ins/hr **DUTY CYCLE** 100% **ELECTROMAGNETIC COMPATIBILITY** In compliance with 2014/30/EU (EMC)(NOTE) In compliance with **LOW VOLTAGE** 2014/35/EU **CLASS OF PROTECTION:** Coil insulation (VDE 0580) class H Impregnation class F

**NOTE**: In order to further reduce the emissions, use of type H connectors is recommended. These prevent voltage peaks on opening of the coil supply electrical circuit (see cat. 49 000).

41 110/118 ED 4/6

### DS2 SERIES 10

#### 10 - OVERALL MOUNTING AND DIMENSIONS



41 110/118 ED 5/6




### DS2 SERIES 10

#### 11 - MANUAL OVERRIDES


#### 11.1 - CM - boot protected manual override

The boot override can be ordered by entering the code  ${\bf CM}$  in the identification code at par. 1, or is available as option to be ordered separately.



#### 11.2 - Knob manual override

The knob override can be ordered by entering the code **CK1** in the identification code at par. 1, or is available as option to be ordered separately.





via M. Re Depaolini 24 • 20015 PARABIAGO (MI) • ITALY tel. +39 0331.895.111 • www.duplomatic.com • e-mail: sales.exp@duplomatic.com